



SPECIFICATION SUBMITTAL SHEET



(with NRS gates)



(with BGVIC valves)



APPLICATION

Designed for installation on potable water lines to protect against both backsiphonage and backpressure of contaminated water into the potable water supply. The Model 375A provides protection where a potential health hazard exists. Ideal for use where lead-free* valves are required.

STANDARDS COMPLIANCE

- ASSE® Listed 1013
- AWWA Compliant C511 (with gates only), and C550
- IAPMO® Listed
- CSA® Certified (2-1/2" - 8")
- UL® Classified
- C-UL® Classified
- FM® Approved
- Approved by the Foundation for Cross Connection Control and Hydraulic Research at the University of Southern California.
- NYC MEA 484-04-M
- NSF® Listed-Standard 61, Annex G*

* (0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

MATERIALS

Main valve body	Ductile Iron ASTM A 536 Grade 4
Access covers	Ductile Iron ASTM A 536 Grade 4
Coatings	FDA Approved electrostatic epoxy finish
Internals	Stainless steel, 300 Series NORYL™, NSF Listed
Fasteners & Springs	Stainless Steel, 300 Series
Seal rings	EPDM (FDA approved)
O-rings	Buna Nitrile (FDA approved)
Sensing line	Stainless Steel, braided hose

FEATURES

Sizes:	<input type="checkbox"/> 2 1/2"	<input type="checkbox"/> 3"	<input type="checkbox"/> 4"	<input type="checkbox"/> 6"	<input type="checkbox"/> 8"	<input type="checkbox"/> 10"
Maximum working water pressure	175 PSI					
Maximum working water temperature	140°F					
Hydrostatic test pressure	350 PSI					
End connections (Grooved for steel pipe)	AWWA C606					
(Flanged)	ANSI B16.1 Class 125					

*2 1/2 & 3" sizes use 4" body & reducer couplings

OPTIONS (Suffixes can be combined)

- with flanged end NRS gate valves (standard)
- FSC - with epoxy coated wye type strainer (flanged only)
- G - with grooved end NRS gate valves
- GF - with grooved inlet gate connection and flanged outlet gate connection
- FG - with flanged inlet gate connection and grooved outlet gate connection
- L - less shut-off valves (grooved body connections)
- MS - with Integral Relief Valve Monitor Switch
- OSY - with flanged end OS&Y gate valves
- OSYG - with grooved end OS&Y gate valves
- BGVIC - with grooved end butterfly valves


ACCESSORIES

- Repair kit (rubber only)
- Thermal expansion tank (Model XT)
- OS & Y Gate valve tamper switch (OSY-40)
- Air gap (Model AG)
- Electronic Solenoid Timer (Model EST)
- QT-SET Quick Test Fitting Set
- Test Cock Lock (Model TCL24)


DIMENSIONS & WEIGHTS (do not include pkg.)

MODEL 375A SIZE	WEIGHT											
	WITHOUT GATES		WITH NRS GATES (GXF)		WITH OS&Y GATES (GXF)		WITH NRS GATES (GXG)		WITH OS&Y GATES (GXG)		WITH BUTTERFLY VALVES (GXG)	
in. mm	lbs. kg	lbs. kg	lbs. kg	lbs. kg	lbs. kg	lbs. kg	lbs. kg	lbs. kg	lbs. kg	lbs. kg	lbs. kg	
2 1/2 65	97 44	191 87	199 90	183 83	191 87	116 53						
3 80	96 43.5	211 96	217 98	201 91	207 94	117 53						
4 100	83 38	227 103	237 108	201 91	211 96	115 52						
6 150	136 62	356 162	372 169	326 148	342 155	188 85						
8 200	305 139	757 344	781 355	757 344	757 344	413 188						
10 250	358 162	985 447	1043 473	863 391	921 418	530 241						

MODEL 375A with OSY & FSC option



MODEL 375A with BGVIC option




Relief Valve discharge port:
2 1/2" - 6" - 2.75 sq. in.
8" - 10" - 3.69 sq. in.

Attention: Model 375A (grooved body) and Model 375 (flange body) have different lay lengths.


MODEL 375A SIZE	DIMENSION (approximate)																								
	A		A WITH BUTTERFLY VALVES		B LESS GATE VALVES		C		D		E OS&Y OPEN		E OS&Y CLOSED		E NRS GATE		E WITH BUTTERFLY VALVES		F		G		H		
	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	
2 1/2	65	35 1/8	892	32 1/8	816	20 1/8	511	4 1/2	114	7 1/4	184	16 3/8	416	13 7/8	352	11 3/8	289	8	203	11	279	45 1/4	1150	7 1/4	184
3	80	36 1/8	918	33	838	20 1/8	511	4 1/2	114	7 1/4	184	18 7/8	479	15 5/8	397	12 3/8	314	8	203	11	279	46 7/8	1191	7 1/4	184
4	100	38 1/4	972	33 1/4	845	19 7/8	505	4 1/2	114	8	203	22 3/4	578	18 1/4	464	14 3/4	375	9 1/8	232	11	279	53 3/8	1356	7 1/4	184
6	150	47 1/4	1200	40 1/4	1022	25 7/8	657	5 1/2	140	10	254	30 1/8	765	23 3/4	603	19	483	10 1/8	257	12 3/8	314	65 3/8	1661	9 1/4	235
8	200	62	1575	55	1397	38 1/2	978	10	254	11	279	37 3/4	959	29 1/4	743	22 1/2	572	11 15/16	303	15 3/8	391	86 3/8	2194	13 7/8	333
10	250	64 5/8	1641	58 1/2	1485	38 1/2	978	10	254	12	305	45 3/4	1162	35 3/8	899	26 1/2	673	13 5/16	338	15 3/8	391	94 3/8	2398	16 7/16	418

FLOW CHARACTERISTICS


MODEL 375A 2-1/2" - 3" (STANDARD AND METRIC)



MODEL 375A 4" & 6" (STANDARD & METRIC)



MODEL 375A 8" & 10" (STANDARD AND METRIC)




◇ Rated Flow (Established by approval agencies)


TYPICAL INSTALLATION

Local codes shall govern installation requirements. Unless otherwise specified, the assembly shall be mounted at a minimum of 12" (305mm) and a maximum of 30" (762mm) above adequate drains with sufficient side clearance for testing and maintenance. The installation shall be made so that no part of the unit can be submerged.

Capacity thru Schedule 40 Pipe (GPM)				
Pipe size	5 ft/sec	7.5 ft/sec	10 ft/sec	15 ft/sec
2 1/2"	75	112	149	224
3"	115	173	230	346
4"	198	298	397	595
6"	450	675	900	1351
8"	780	1169	1559	2339
10"	1229	1843	2458	3687
12"	1763	2644	3525	5288



INDOOR INSTALLATION (375A with BGVIC option)



OUTDOOR INSTALLATION (375A with FSC option)

SPECIFICATIONS

The Reduced Pressure Principle Backflow Prevention Assembly shall be ASSE® Listed 1013, and supplied with full port gate valves. The main body and access cover shall be epoxy coated ductile iron (ASTM A 536 Grade 4), the seat ring and check valve shall be NORYL™, the stem shall be stainless steel (ASTM A 276) and the seat disc elastomers shall be EPDM. The checks and the relief valve shall be accessible for maintenance without removing the device from the line. The Reduced Pressure Principle Backflow Prevention Assembly shall be a WILKINS Model 375A.

WILKINS a Zurn company, 1747 Commerce Way, Paso Robles, CA 93446 Phone: 805/238-7100 Fax: 805/238-5766

IN CANADA: ZURN INDUSTRIES LIMITED, 3544 Nashua Dr., Mississauga, Ontario L4V 1L2 Phone: 905/405-8272 Fax: 905/405-1292